

AMT8304

2.125 Gb/s Integrated 850nm MSM-TIA PRELIMINARY DATA SHEET - Rev 1.1

FEATURES


- Differential Output TIA
- 3.3V Operation
- Automatic Gain Control
- Integrated 850nm MSM Detector & TIA
- TO-46 Ultra Flat-Window or Lens Hermetic Package
- High Reliability

APPLICATIONS

• 2x Fibre Channel (2.125 Gb/s)

PRODUCT DESCRIPTION

The ANADIGICS AMT8304 is a 3.3V monolithically integrated Metal-Semiconductor-Metal (MSM) photodetector and transimpedance amplifier (TIA) used to convert an 850nm input optical signal into a differential output voltage, and is manufactured in ANADIGICS' 6" GaAs wafer fabrication facility. The integrated MSM and TIA receiver maximizes the receiver performance by minimizing the photodetector input parasitics to the TIA and



internally biasing the photodetector to achieve high sensitivity, bandwidth and overload performance. As an integrated product the reliability is inherently better than a discrete solution, and both the MSM-TIA integrated circuit and TO-46 flat window and TO-46 lens packaged receiver pass stringent reliability requirements. These products are readily designed into receivers and transceivers for 2x Fibre Channel applications.




Figure 1: Equivalent Circuit




Figure 2: T46F/T46L/T4TL Pin Outline (Bottom View)

PIN	DESCRIPTION	COMMENT
1	V _{out} - TIA Output Voltage (non-Inverted)	Logical '1' with optical input
2	V _{DD} - Positive Supply Voltage	+3.3 Volts
3	V _{out} - TIA Output Voltage (Inverted)	Logical '0' with optical input
4	Ground	Case is grounded

Table 1: Package PIN Description

ELECTRICAL CHARACTERISTICS

Table 2: Absolute Maximum Ratings

V _{DD}	6.0V
P _{IN}	+5dBm
Ts	Storage Temp65 °C to 125 °C

Stresses in excess of the absolute ratings may cause permanent damage. Functional operation is not implied under these conditions. Exposure to absolute ratings for extended periods of time may adversely affect reliability.

PARAMETER	MIN	TYP	MAX	UNIT
Wavelength (λ)	770	850	860	nm
Detector Diameter	-	100	-	μm
Small Signal Differential Responsivity ⁽¹⁾ (@ 50 MHz)	1000	-	-	V/W
Bandwidth (1)	1400	1900	-	MHz
Low Frequency Cutoff	-	-	300	KHz
Output Resistance	-	40	-	
Optical Overload (2)	0	-	-	dBm
Optical Sensitivity (2)	-19	-	-	dBm
Differential Output Voltage (3)	-	750	-	mV
$T_{_{\text{RISE}}}$ and $T_{_{\text{FALL}}}$ (20-80%) $^{\scriptscriptstyle (3)}$	-	140	-	ps
Duty Cycle Distortion (3)	-	5	-	%
Total Jitter (3),(4)	-	50	-	ps
Supply Current	-	35	55	mA
Operating Voltage Range	+3.0	+3.3	+3.6	Volts
Operating Case Temperature Range	0	-	80	°C

Table 3: Electrical Characteristics

Notes:

(1) Measured at -14 dBm optical input power with output connected into $R_{L} = 100\Omega$ (differential) (2) Measured at 10^{-10} BER with a 2^{7} -1 PRBS at 2.125 Gb/s (3) Measured with a 2^{7} -1 PRBS at 2.125 Gb/s, an input optical power of -3dBm and $R_{L} = 100 \ \Omega$ (differential) (4) 6σ about the center eye crossing

PERFORMANCE DATA

Figure 3: Eye Diagram with an Optical Input Power of –19dBm (with a 4GHz LPF)






Figure 4: Eye Diagram with an Optical Input Power of -9.0dBm



50mV/Div.

100ps/Div

Figure 5: Eye Diagram with an Optical Input Power of 0dBm







Figure 6: Supply Current vs. Temperature

Figure 7: Bandwidth vs. Temperature







MEASUREMENT METHODS




Figure 11: Test Setup for Frequency Response

BERT




Figure 12: Test Setup for Sensitivity




Figure 13: Test Setup for Eye Measurements





Figure 13: DUT Test Fixture Schematic

APPLICATION INFORMATION





 $C_{\rm F}$ is an optional single pole noise filter

$$C_{\rm F} = \frac{1}{2\pi f_c R}$$


 f_c is the desired cutoff frequency

 $R = 50 \ \Omega$

 R_o is required with high input resistance limiting amplifiers

$$R_{o} = 100 \ \Omega$$

PACKAGE OUTLINE



MM CONTROLLING DIMENSIONS

SYMBOL	INC		MILLIM		
"0 _L	MIN.		MIN.		
А	0.098	0.110	2.50	2.80	
øb	0.016		0.41	0.51	1
øb2	0.012	0.019		0.48	1
øD	0.212	0.218	5.38	5.54	
ØDi	0.181	0.187	4.60	4.75	
е	0.100) T.P.	2.54	T.P.	2
е 1	0.050) T.P.	1.27	T.P.	2
h	0.014	0.022	0.36	0.56	
1		0.540	12.70	13.70	1
1 1	-		_	1.27	1
12	0.250	-	6.35	-	1

NOTES

- 1. (FOUR LEADS) #b2 APPLIES BETWEEN 1: AND 12. ob APPLIES BETWEEN 12 AND 0.5 [12.70mm] FROM SEATING PLANE. DIAMETER IS UNCONTROLLED IN 1: AND BEYOND 0.5 [12.70mm] TO END OF PIN.
- 2. MAXIMUM DIAMETER LEADS AT A GAGING PLANE 0.054 [1.37mm]+0.001 [0.025mm] -0.000 [0.000mm] BELOW SEATING PLANE TO BE WITHIN 0.007 [0.178mm] OF THEIR TRUE POSITION RELATIVE TO MAXIMUM-WIDTH TAB AND TO THE MAXIMUM 0.212 [5.40mm] DIAMETER MEASURED WITH A SUITABLE GAGE. WHEN GAGE IS NOT USED, MEASUREMENT WILL BE MADE AT 0.250 [6.35mm] FROM SEATING PLANE.
- 3. INTERNAL OPTICAL HEIGHT = $0.052 \pm 0.003 [1.31 \pm .08]$
- BENT LEADS SHOULD NOT EXTEND OUTSIDE DIAMETER (©D) OF CAP OR TOUCH EACH OTHER.
- 5. ALL DIMENSIONS ARE REFERENCE ONLY-EXCEPT A, D & h.
- DETECTOR DIODE PLACEMENT ACCURACY ⊕0.15MM[0.006] WITH RESPECT TO CENTER OF HEADER.(REF.ONLY)

Figure 15: T46F Package Outline Diagram




Figure 16: T46L Package Outline Diagram




Figure 17: T4TL Package Outline Diagram

NOTES

ORDERING INFORMATION

ORDER NUMBER	PACKAGE OPTION	PACKAGE DESRIPTION
AMT8304T46F	TO-46F	Ultra Flat Window Package
AMT8304T46L	TO-46L	Lens Package
AMT8304T4TL	TO-46L	Lens Package with Tabbed Header

ANADIGICS

ANADIGICS, Inc.

141 Mount Bethel Road Warren, New Jersey 07059, U.S.A. Tel: +1 (908) 668-5000 Fax: +1 (908) 668-5132

URL: http://www.anadigics.com E-mail: Mktg@anadigics.com

IMPORTANT NOTICE

ANADIGICS, Inc. reserves the right to make changes to its products or to discontinue any product at any time without notice. The product specifications contained in Advanced Product Information sheets and Preliminary Data Sheets are subject to change prior to a product's formal introduction. Information in Data Sheets have been carefully checked and are assumed to be reliable; however, ANADIGICS assumes no responsibilities for inaccuracies. ANADIGICS strongly urges customers to verify that the information they are using is current before placing orders.

WARNING

ANADIGICS products are not intended for use in life support appliances, devices or systems. Use of an ANADIGICS product in any such application without written consent is prohibited.