


# PS3153 / PS3154 <u>Li Ion Smart Battery Manager</u> <u>Module with Safety</u>

## Features

- Standard sized modules for assembly into custom and standard sized battery packs
- Designed to work with 3cell (3153) and 4 cell (3154) series Li Ion configurations
  - Performs all major Li Ion battery management functions.
- On-board Mitsumi safety circuit provides
   one or two levels of safety
- Fully compliant with industry standard Smart Battery Data Specification V1.1a
  - SMBus V1.1 with PEC / CRC-8 communication with system host
- High accuracy measurement of charge / discharge current, voltage, and temperature with on-chip 14-bit integrating A/D
- Precise capacity reporting using PowerSmart patented algorithms and 3D battery cell models
- 3D models and "learned" parameters stored in on board EEPROM; fully field reprogrammable via SMBus interface
- Extremely low power operation:
  - Sleep Mode: < 10 uA typical
  - Run Mode: < 500 uA typical
  - Sample Mode < 250 uA typical
- Complete hardware and software development tools available

## PCB Assembly



## **Ordering Information**

Pre-tested, fully assembled modules are available:

PS3153 – 3 cell Li Ion module PS3154 – 4 cell Li Ion module

## **Quick Start**

Follow these directions to assemble a pack with the PS3150 module. Use standard precautions when handling static sensitive devices.

- Modules should be connected to battery cells in the order indicated below to insure proper start-up and operation. Wires should be attached to the modules first and then connected to the battery cells as instructed.
- The connection sequence is critical to successful use of the PS331 family of CMOS ASICs. The
  negative cell string connection should always be connected first, followed by the cell string
  positive connection. The remaining connections can then be made after the pack negative and
  pack positive are securely connected to the module.

**Step 1)** Configure the module jumpers according to the following chart:

	Li Ion 3-cell	Li Ion 4-cell
R27	Removed	Installed
R28	Installed	Removed
R30	Installed	Removed

**Step 2)** Connect wires to module. Use large diameter wire (18AWG-20 AWG) for current carrying lines from W1 and W5. All others are signal only lines (24 to 22 AWG).


Step 3) Connect W1 (BN) to the most negative point on the battery cell stack.

**Step 4)** Connect W5 (BP) to the most positive point on the battery cell stack.

Step 5) Li Ion Only: Connect cell voltage pickups:

4 series cells - Vcell1 to W2, Vcell2 to W3, and Vcell3 W4 3 series cells - Vcell1 to W3, Vcell2 to W4, No Conn at W2

Step 6) Connect external connector to B-Neg, T, C, D and B-Pos .



- Step 7) Program the assembled pack using PowerSmart's SBTool software and calibration board or info board hardware and your \*.p3I file. Default \*.p3I files are available on the website (www.powersmart.com).
- **Step 8)** Calibrate the pack using the SBTool software and calibration board hardware. The pack is now ready for use.

## **General Description**

The PS3150 module is a SBS V1.1 compliant smart battery controller. The module is designed to operate in a battery pack consisting of three or four series connected Lithium Ion cells. The module consists of three major circuit sections - the PowerSmart PS331 SMBus fuel gauge, Mitsumi MM1253/4 based primary safety circuit and a secondary safety circuit controlled by the PS331 to provide backup to the MM1253/4.


## **Functional Description**

P3 Fuel Gauge - The module fuel gauge provides State-of-Charge (SOC) and battery status data in accordance with the SBData and SMBus standards version 1.1. The PS331 monitors the cell voltages, battery temperature, and current to determine SOC and battery status. The PS331 also provides remaining\_time, terminate\_charge, and terminate\_discharge alarms when the battery is fully discharged, fully charged or is under conditions of over-temperature, over-voltage or overdischarge. The State-of-Charge calculations are compensated for cell self discharge. The remaining time calculation is compensated for temperature and discharge rate. An additional correction is made in the SOC for the estimated integration errors, reported as Max\_Error. The parameters for determining battery status flags and alarm thresholds are all programmable as is the battery design capacity and the battery performance model data. Please refer to the 'P3 Users Guide" and the 'PS331 Technical Data Sheet' for details on programming the P3 serial EEPROM data (programmable EEPROM data is capitalized in this text for clarity).

Primary Safety -The primary safety circuit provides cell protection from conditions of overcharge, overdischarge and overcurrent. The analog IC MM1253/4 from Mitsumi measures individual cell voltages and voltage across the discharge FET. These measures are compared against internal reference values and the gates of two P-channel power MOSFETs are controlled based on the comparison results.

Secondary Safety – The second level of safety protection is activated by Safeout (pin 21) of the PS331. This pin is activated whenever any individual cell voltage is measured above a programmable limit. An N-channel MOSFET is turned on and allows current to pass through the resistive heater section of a fuse. This heating opens the fuse, permanently disabling the pack from further charge or discharge.

# **Board Schematics**



## **Bill of Materials**

UNLESS OTHERWISE NOTED: RESISTORS ARE 5% TOLERANCE; VALUES IN OHMS CAPACITORS ARE: COG -- +/-5%; X7R -- +/-10%; Y5V -- +80%/-20%

NDEX	REF. DES.	PART TYPE	VALUE	PACKAGE	QTY.	MANUFACTURER	MFR. PART NUMBER
2		FABRICATION		RAW BOARD	1	POWERSMART	B826032-07-03
	C1 C3	CAPACITOR	330nf/X7R/25V	3216[1206]	2	VARIOUS	
	C8	CAPACITOR	100nF/X7R/25V	2012[0805]	1	VARIOUS	
	C10	CAPACITOR	2.2nF/X7R/50V	1608[0603]	1	VARIOUS	
	C2 C5 C11 C12 C13 C14 C15 C16 C17 C18 C19 C23		100nF/Y5V/25V	1608[0603]	12	VARIOUS	
		CAPACITOR	47pF/C0G/50V	1608[0603]	1	VARIOUS	
			22pF/C0G/50V	1608[0603]		VARIOUS	*
	C9		10nF/X7R/25V	1608[0603]		VARIOUS	
	D1 D2 D3 D4		CCL-LX45GT	LED\TR8		LUMEX	CCL-LX45GT
			ZMM5257B	DO-213AA\PS	3	DIODES, INC.	ZMM5257B
1	106107		BZX84C5V6	SOT23	2	DIODES, INC. ZETEX	BZX84C5V6 BZX84C5V6
2	D8		BAT54C	SOT23		VARIOUS	
3	D9		SMBJ20A	SMB	1	DIODES, INC. CRYDOM	<u>SMBJ20A</u> SMBJ20A
1	F1	FUSE (5A)	SFC1605A	FUSE\SCP	1	SONY CHEMICALS	SFC1605A
5	Q1	MOSFET	2N7002	SOT23-GSD	1	VARIOUS	
	Q2 Q3	MOSFET	IRF7416	SO8	2	INT. RECTIFIER	IRF7416
,	Q4	TRANSISTOR	2N3906	SOT23-BEC	1	VARIOUS	
	Q5		NDS355N	SOT23-GSD		FAIRCHILD SEMI.	NDS355N
			5HP01M	SOT23		SANYO	5HP01M
			10K Thermistor	1608[0603]		SEMITEC	103KT1608-2P
			4.7M	1608[0603]		VARIOUS	
			25 mOhms (0.5%)	WSL2512		VISHAY	WSL2512-0.025- 0.5%-R86
3	R5 R7 R13	RESISTOR	330	1608[0603]	3	VARIOUS	
			220	1608[0603]		VARIOUS	
			2M	1608[0603]		VARIOUS	
			200K	1608[0603]		VARIOUS	
			365 (1%)	1608[0603]		VARIOUS	
			20K	1608[0603]		VARIOUS	
		RESISTOR	470	1608[0603]		VARIOUS	
			0 Ohm	1608[0603]		VARIOUS	
			3.65K (1%)	1608[0603]		VARIOUS	
			56	1608[0603]		VARIOUS	
			510	1608[0603]		VARIOUS	
		RESISTOR	100	1608[0603]		VARIOUS	
	S1		SW\EVQPS\MTG	SW\EVQPS\MTG		PANASONIC	EVQ-PSD02K
	U1		PS331S	SSOP28		POWERSMART	PS331S
			M25LC040	SO8		MICROCHIP	25LC040-I/SN
	U3		MM1414DV	TSOP-20A		MITSUMI	MM1414DV
		CRVSTAL	32.768 KHz (100 ppm, 12-12.5pF)				MX1V-TL-32.768H 12.5pF-100ppm C-002RX 32.7680 <u>A **</u> VT-200 12.5pF ** CMR200TB 12.5p
T U1, (2) A * NOT	<u>AND</u> N EPSON, SEIKO, O		WHEN (1) A VERSION YSTAL IS USED IN SU S ARE NOT SUITABLE	ICH AN ASSEMB	BLY.		3.5 IS INSTALLED

## **Development Tool Summary**

PowerSmart provides all the necessary hardware and software to enable easy tailoring of battery control algorithm parameters and cell performance models to meet specific application requirements and attain the highest accuracy available anywhere. Table 1 summarizes the development tool offering from PowerSmart to support the PS331. Please refer to the PowerSmart web site for ordering information and design documentation (including schematics) at <u>www.powersmart.com</u>.


#### **Reference Documents**

This data sheets provides an overview of the PS3150 Li Ion Module. It provides a detailed description of features and specifications that are unique to the PS3150. For further information on P3 device and development tool operations, please refer to the following documents available for download at <a href="http://www.powersmart.com">www.powersmart.com</a>:


PS331 Data Sheet P3 Family User's Guide Applications Notes: P3 Ex. Connection Diagrams P3 PC Board Layout Guide P3 Temperature Alarm Operation P3 Calibration Explanations Development Tool Documentation: Lithium Ion Workbook Guide SBTool User's Guide P3 Eval System Data Sheet P3 Cal System Data Sheet P3 Info / Test Board Data Sheet SBToolBox Data Sheet

## Mechanical Dimensions (units are mils)


Top layer



Bottom layer



Dimensions



## **Quality Control**

PowerSmart, Inc., has received ISO-9001 certification through TUV Rheinland of North America, based in Newtown, Conn. ISO-9001 certification indicates that PowerSmart has met strict international standards of quality control in manufacturing systems including product design, production, training, and inspection and testing. PowerSmart received certification for a quality system for the Design and Development of Battery Control Integrated Circuits, Software, Modules, Chargers, and Systems. PowerSmart, Inc., provides smart battery and charger electronics designed for use with all battery chemistries, bringing a new level of accuracy, reliability and customization not available before with other smart battery ICs.

#### Notice

PowerSmart products are not authorized for use as critical components of life support devices or systems. Seller disclaims any warranty or responsibility for such usage, which shall be at buyer's sole risk, notwithstanding any prior notice to seller of such usage or intended usage.

As used herein, "life support devices or systems" are devices or systems that are intended for implant, and whose failure to perform in such function can be reasonably expected to result in significant injury to the user. A "critical component" is any component of a life support device or system whose failure to perform can reasonably be expected to cause or result in the failure of performance of a life support device or system or to adversely affect its safety or effectiveness.